

## **DuPont™ Kapton® HN**

### Polyimide Film

#### Description

DuPont™ Kapton® HN general-purpose film has been used successfully in applications at temperatures as low as -269°C (-452°F) and as high as 400°C (752°F). HN film can be laminated, metallized, punched, formed or adhesive coated. Kapton® HN is the recommended choice for applications that require an all-polyimide film with an excellent balance of properties over a wide range of temperatures.

#### **Applications**

- Mechanical parts
- · Electronic parts
- · Electrical Insulation
- · Pressure sensitive tape

- · Fiber optics cable
- · Insulation blankets
- Insulation tubing
- · Automotive diaphragms sensors and manifolds
- Etching
- Shims

#### **Product Specifications**

Kapton® HN is manufactured, slit and packaged according to the product specifications listed in H-38479 (6/18).

#### Certification

Kapton® HN meets ASTM D-5213 (type 1, item A) requirements.

Table 1 – Physical Properties of DuPont™ Kapton® HN at 23°C (73°F)

Ultimate Tensile Strength at 23°C (78°F)	Property	Unit	.05 mil 12.7µm	1 mil 25µm	2 mil 50µm	3 mil 75µm	5 mil 125µm	Test Method
at 220°C (32°C)         %         65         72         72         78         82         ASTM D-882-91, Method A           Tensile Modulus at 28°C, (73°F)         psi (GPa)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         400,000 (2.76)         ASTM D-882-91, Method A           Tensile Modulus at 20°C (392°F)         g/cc         142         142         142         142         142         142         290,000 (2.0)	at 23°C, (73°F)	psi (MPa)	, , ,	, , ,	, , ,	, , ,	, , ,	ASTM D-882-91, Method A*
at 23°C, (73°F) at 29°C, (73°F)         psi (GPa) (160,000 (110) (160,000 (2.76) (160,000 (2.76) (290,000 (2.0) (2.0)	at 23°C, (73°F)	%						ASTM D-882-91, Method A
MIT Folding Endurance         cycles         >285,000         285,000         55,000         6,000         5,000         ASTM D-2176-89           Tear Strength-propagating (Elmendorf), N (lbf)         NA         0.07 (0.02)         0.21 (0.02)         0.38 (0.02)         0.58 (0.02)         ASTM D-1922-89           Tear Strength, Initial (Graves), N (lbf)         3.5 (1.6)         7.2 (1.6)         16.3 (1.6)         26.3 (1.6)         46.9 (1.6)         ASTM D-1004-90           Yield Point at 3% at 23°C, (73°F) at 20°C (392°F)         MPa (psi)         69 (10,000) 69 (10,000) 41 (6,	at 23°C, (73°F)	psi (GPa)	, , ,	, , ,	, , ,	, , ,	, , ,	ASTM D-882-91, Method A
Tear Strength-propagating (Elmendorf), N (lbf)  Tear Strength, Initial (Graves), N (lbf)  3.5 (1.6)  7.2 (1.6)	Density	g/cc	1.42	1.42	1.42	1.42	1.42	ASTM D-1505-90
(Elmendorf), N (lbf)         NA         0.07 (0.02)         0.21 (0.02)         0.38 (0.02)         0.58 (0.02)         ASTM D-1922-89           Tear Strength, Initial (Graves), N (lbf)         3.5 (1.6)         7.2 (1.6)         16.3 (1.6)         26.3 (1.6)         46.9 (1.6)         ASTM D-1004-90           Yield Point at 3% at 23°C, (73°F) at 200°C (392°F)         MPa (psi)         69 (10,000)	MIT Folding Endurance	cycles	>285,000	285,000	55,000	6,000	5,000	ASTM D-2176-89
Yield Point at 3% at 23°C, (73°F) at 20°C (392°F)         MPa (psi)         69 (10,000) 41 (6,000)         69 (10,000) 41 (6,000)         69 (10,000) 41 (6,000)         ASTM D-882-91           Stress to produce 5% elong. at 23°C, (73°F) at 200°C (392°F)         MPa (psi)         90 (13,000) 90 (13,000	5 5 5		NA	0.07 (0.02)	0.21 (0.02)	0.38 (0.02)	0.58 (0.02)	ASTM D-1922-89
at 23°C, (73°F) MPa (psi) 69 (10,000) 69 (10,000) 69 (10,000) 69 (10,000) 69 (10,000) 69 (10,000) ASTM D-882-91 At 16,000)  Stress to produce 5% elong. at 23°C, (73°F) MPa (psi) 90 (13,000) 90 (13,000) 90 (13,000) 90 (13,000) 90 (13,000) 62 (9,000)  Impact Strength at 23°C, (73°F) N· cm· (ft lb) 78 (0.58) 78 (0.58) 78 (0.58) 78 (0.58) 78 (0.58) DuPont Pneumatic Impact Test  Coefficient of Friction, kinetic (film-to-film)  Coefficient of Friction, static (film-to-film)  Refractive Index (sodium D line)  1.70 1.70 1.70 1.70 1.70 1.70 ASTM D-542-90  Poisson's Ratio	Tear Strength, Initial (Graves), N (lbf)		3.5 (1.6)	7.2 (1.6)	16.3 (1.6)	26.3 (1.6)	46.9 (1.6)	ASTM D-1004-90
at 23°C, (73°F) MPa (psi) 90 (13,000) 90 (	at 23°C, (73°F)	MPa (psi)	. , ,	. , ,	. , ,	. , ,	. , ,	ASTM D-882-91
Coefficient of Friction, kinetic (film-to-film)         0.48         0.48         0.48         0.48         0.48         ASTM D-1894-90           Coefficient of Friction, static (film-to-film)         0.63         0.63         0.63         0.63         0.63         ASTM D-1894-90           Refractive Index (sodium D line)         1.70         1.70         1.70         1.70         1.70         ASTM D-542-90           Poisson's Ratio         0.34         0.34         0.34         0.34         0.34         Avg. three samples, elongated at 5, 7, 10%	at 23°C, (73°F)	MPa (psi)	. , ,	. , ,	. , ,	. , ,	. , ,	ASTM D-882-92
(film-to-film)         0.48         0.48         0.48         0.48         0.48         ASTM D-1894-90           Coefficient of Friction, static (film-to-film)         0.63         0.63         0.63         0.63         ASTM D-1894-90           Refractive Index (sodium D line)         1.70         1.70         1.70         1.70         ASTM D-542-90           Poisson's Ratio         0.34         0.34         0.34         0.34         Avg. three samples, elongated at 5, 7, 10%	Impact Strength at 23°C, (73°F)	N· cm· (ft lb)	78 (0.58)	78 (0.58)	78 (0.58)	78 (0.58)	78 (0.58)	DuPont Pneumatic Impact Test
(film-to-film)         0.63         0.63         0.63         0.63         ASTM D-1894-90           Refractive Index (sodium D line)         1.70         1.70         1.70         1.70         ASTM D-542-90           Poisson's Ratio         0.34         0.34         0.34         0.34         Avg. three samples, elongated at 5, 7, 10%			0.48	0.48	0.48	0.48	0.48	ASTM D-1894-90
Poisson's Ratio         0.34         0.34         0.34         0.34         Avg. three samples, elongated at 5, 7, 10%	•		0.63	0.63	0.63	0.63	0.63	ASTM D-1894-90
	Refractive Index (sodium D line)		1.70	1.70	1.70	1.70	1.70	ASTM D-542-90
Low temperature flex life pass pass pass pass pass pass IPC-TM-650, Method 2.6.18	Poisson's Ratio		0.34	0.34	0.34	0.34	0.34	Avg. three samples, elongated at 5, 7, 10%
	Low temperature flex life		pass	pass	pass	pass	pass	IPC-TM-650, Method 2.6.18

<sup>\*</sup>Specimen size 25 x 150 mm (1.6 in); jaw separation 100 mm (4 in), jaw speed, 50mm/min (2 in/min). Ultimate refers to the tensile strength and elongation measured at break.

Table 2 – Thermal Properties of DuPont $^{\text{\tiny{M}}}$  Kapton $^{\text{\tiny{0}}}$  HN Film

Thermal Property	Typical Value	Test Condition	Test Method	
Melting Point	None	None	ASTM E-794-85 (1989)	
Thermal Coefficient of Linear Expansion	20 ppm/°C (11 ppm/°F)	-14 to 38°C (7 to 100°F)	ASTM D-696-91	
Coefficient of Thermal Conductivity, W/m· K  cal  cm· sec· °C	0.12 2.87 x 10 <sup>4</sup>	296K 23°C	ASTM F-433-77 (1987)	
Specific Heat, J/g•K (cal/g·°C)	1.09 (0.261)		Differential calorimetry	
Heat Sealability	not heat sealable			
Solder Float	pass		IPC-TM-650 Method 2.4.13A	
Smoke Generation	D <sub>m</sub> =<1	NBS smoke chamber	NFPA-258	
Shrinkage, % 30 min at 150°C 120 min at 400°C	0.17 1.25		IPC-TM-650 Method 2.2.4A; ASTM D-5214-91	
Limiting Oxygen Index, %	37–45		ASTM D-2863-87	
Glass Transition Temperature (Tg)	A second order transition occurs in Kapton® between 360°C (680°F) and 410°C (770°F) and is assumed to be the glass transition temperature. Different measurement techniques produce different results within the above temperature range.			

Table 3 – Typical Electrical Properties of DuPont™ Kapton® HN Film at 23°C (73°F), 50% RH

Property Film Gage	perty Film Gage Typical Value		Test Condition	Test Method
Dielectric Strength 12.7 μm (0.5 mil) 25 μm (1 mil) 50 μm (2 mil) 75 μm (3 mil) 125 μm (5 mil)	V/m kV/mm 315 303 240 201 154	(V/mil) (8000) (7700) (6100) (5100) (3900)	60 Hz 1/4 in electrodes 500 V/sec rise	ASTM D-149-91
Dielectric Constant 12.7 μm (0.5 mil) 25 μm (1 mil) 50 μm (2 mil) 75 μm (3 mil) 125 μm (5 mil)	3.4 3.4 3.4 3.5 3.5		1 kHz	ASTM D-150-92
Dissipation Factor 12.7 μm (0.5 mil) 25 μm (1 mil) 50 μm (2 mil) 75 μm (3 mil) 125 μm (5 mil)	0.0016 0.0018 0.0020 0.0020 0.0026		1 kHz	ASTM D-150-92
Volume Resistivity 12.7 μm (0.5 mil) 25 μm (1 mil) 50 μm (2 mil) 75 μm (3 mil) 125 μm (5 mil)	$\Omega$ -cm <sup>17</sup> 1.5 x 10 <sup>17</sup> 1.5 x 10 <sup>17</sup> 1.5 x 10 <sup>17</sup> 1.5 x 10 <sup>17</sup> 1.4 x 10 <sup>17</sup> 1.0 x 10 <sup>17</sup>			ASTM D-257-91

#### **Dimensional Stability**

The dimensional stability of DuPont™ Kapton® polyimide film depends on two factors—the normal coefficient of thermal expansion and the residual stresses placed in the film during manufacture. The latter causes Kapton® to shrink on its first exposure to elevated temperatures as indicated in the bar graph in **Figure 1.** Once the film has been exposed, the normal values of the thermal coefficient of linear expansion as shown in **Table 4** can be expected.

Figure 1. Residual Shrinkage vs. Exposure Temperature and Thickness, DuPont™ Kapton® HN




Table 4 – Thermal Coefficient of Expansion, DuPont™ Kapton® HN Film, 25 µm (1 mil), Thermally Exposed

Temperature Range, °C, (°F)	ppm/°C
30–100 (86–212)	17
100-200 (212-392)	32
200–300 (392–572)	40
300-400 (572-752)	44
30-400 (86-752)	34



electronics.dupont.com

# For more information on DuPont™ Kapton® or other DuPont products, please visit our website.

The information provided in this data sheet corresponds to our knowledge on the subject at the date of its publication. It may be subject to revision as new knowledge and experience becomes available. This information is not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of our products for your particular purposes. Since we cannot anticipate all variations in end-use and disposal conditions, DuPont makes no warranties and assumes no liability in connection with any use of this information. It is intended for use by persons having technical skill, at their own discretion and risk. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent right.

CAUTION: Do not use in medical applications involving permanent implantation in the human body. For other medical applications, see "DuPont Medical Caution Statement," H-50102-5 and "DuPont Policy Regarding Medical Applications" H-50103-5.

DuPont<sup>™</sup>, the DuPont Oval Logo, and all products, unless otherwise noted, denoted with <sup>™</sup>, <sup>™</sup> or <sup>®</sup> are trademarks, service marks or registered trademarks of affiliates of DuPont de Nemours, Inc. Copyright © 2019 DuPont de Nemours Inc. All rights reserved.